



Sporicidin[®] Enzyme Cleaner Concentrate

Highly concentrated solution



Description

A combination of protease (to remove protein), amylase (to remove starch), lipase (to remove fat), and surfactants.

Softens organic contamination for easier removal. Makes blood and other dried organic matter easier to remediate. Works well with smoke from fires, dirt and oily residue from floods, sewage residue, pet stains and pet odors, as well as some chemical residues. Makes scrubbing and removal of contamination easier.

Recommended for use on floors, walls, ceilings, painted surfaces, metal, tile, concrete, cinder block, brick, carpet, fabric, upholstery, plastic, glass, vinyl, latex, wood studs, joists, beams, sub floors, and other materials subject to moisture.

Ideal for use with a foamer for flood damage restoration.

Technical Data

ATTRIBUTES	Value	Notes
pH	7.5	Mild Alkaline

Part Number	Description	Packaging
ENZ-3212	Sporicidin Enzyme Mold Cleaner, 0.95 liter (US 32 ounce)	12 each/case
ENZ-MOLD55GAL	Sporicidin Enzyme Mold Stain Cleaner, 208-liter (US 55 gallon) drum	4 drums/pallet



Notes:

- 1) The information presented here is applicable to the part numbers shown above as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 1/10/18



Directions for Use:

Add 50 ml of ENZ-3212 or ENZ-MOLD55GAL to a liter of potable water and apply solution to surface or material to be cleaned. Allow at least one minute of contact time, product continues to work as long as the surface is wet. Remove debris. Stubborn or heavy contamination may require repeat application or a higher concentration of 100 ml per liter of potable water.

Biohazard treatment - Add up to 200 ml of concentrate per liter of potable water to soften and remove dried blood and remains. Apply with a foamer to treat vertical surfaces such as walls, ceilings and refrigerator surfaces. Increase dwell time of foam to soften and loosen stubborn contamination.

Mold contamination and remediation – Follow industry guidelines for mold remediation. Use *Sporicidin® Enzyme Mold Stain Cleaner* for easy cleaning of mold stains. Use other Contec® products like *Sporicidin® Disinfectant Solution Spray* or *Towelettes* to disinfect surfaces and equipment after cleaning or *Sporicidin® Mold Resistant Coating* to protect surfaces.

Carpets, rugs and fabrics – To remove spots or stains, apply diluted solution to soiled areas. Absorb excess with clean cloth or paper towels. Carpets: Apply diluted solution to carpets using a pressure sprayer (up to 25 square meters per diluted liter). Extract with carpet cleaning machine and dry carpets using fans or air-movers. Use wooden blocks or carpet tabs to protect furniture until carpets are dry. Stubborn stains may require applications. Confirm color fastness of carpet or rug in a small inconspicuous area before broad application.

Septic system maintenance – Flush 8 liters of diluted solution into toilet nearest to septic tank once a month to keep septic system from backing up and to keep filed lines clear.

Evacuation systems – Circulate through hoses daily for 1-2 minutes to maintain cleanliness.

Precautions:

Keep Out of Reach of Children. Avoid contact with eyes. If product comes in contact with eyes, immediately rinse with clean water for at least 10 minutes.

Storage: Store between 10-40°C or 50-104°F.

Disposal: Flush used solution down the regular drain. Dispose of container in regular trash, according to local regulations.

Notes:

- 1) The information presented here is applicable to the part numbers shown above as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 1/10/18



Copyright © 2018 Contec, Inc. All rights reserved.

P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
Fax: +1-864-503-8444
Toll free US, Canada, PR: 1-800-289-5762

Customer Service
United States: 1-866-855-4682
Europe/Asia: +1-864-699-8257
e-mail: wipers@contecinc.com
www.contecinc.com